

**Garant**
**Clamping toolholder PCKNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 32/19mm**

**Order data**

Order number	250023 32/19
GTIN	4045197782656
Item class	21T

**Technical description**

suitable indexable insert	CN.. 1906..
Overall length L	170 mm
Shim pins pack	259044 7
Shim	259031 36
Lever	259015 13
Lever screw	259018 13
Shim punches pack	259047 5
ISO code toolholder	PCKNR/L 3232P19
Shank size	32 mm
Functional width L <sub>4</sub>	40 mm
Head length L <sub>1</sub>	40 mm
Insert size	19 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 13	259015 13
Lever screw Type 13	259018 13
Shim Type 36	259031 36
Set of shim pins 10 pieces Type 7	259044 7