

Garant
**Clamping toolholder PCSNR 45°, for indexable inserts CN., right-hand,
Shank / insert size: 16/09mm**

Order data

Order number	250024 16/09
GTIN	4045197782694
Item class	21T

Technical description

Shim pins pack	259044 5
Shim	259031 27
Insert size	9 mm
Shank size	16 mm
suitable indexable insert	CN.. 09T3..
ISO code toolholder	PCSNR/L 1616H09
Lever screw	259018 6
Functional width L ₄	20 mm
Overall length L	100 mm
Lever	259015 9
Head length L ₁	22 mm
Shim punches pack	259047 3
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3