

**Garant**

**Clamping toolholder PCSNR 45°, for indexable inserts CN., right-hand,  
Shank / insert size: 20/09mm**



### Order data

Order number	250024 20/09
GTIN	4045197782700
Item class	21T

### Technical description

Shim punches pack	259047 3
Lever screw	259018 6
ISO code toolholder	PCSNR/L 2020K09
Functional width L <sub>4</sub>	25 mm
Shim pins pack	259044 5
Head length L <sub>1</sub>	26 mm
Shank size	20 mm
Shim	259031 27
Lever	259015 9
suitable indexable insert	CN.. 09T3..
Insert size	9 mm
Overall length L	125 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3