

Garant

**Clamping toolholder PCSNR 45°, for indexable inserts CN., right-hand,
Shank / insert size: 25/09mm**



Order data

Order number	250024 25/09
GTIN	4045197782717
Item class	21T

Technical description

Shim punches pack	259047 3
Insert size	9 mm
ISO code toolholder	PCSNR/L 2525M09
Shank size	25 mm
suitable indexable insert	CN.. 09T3..
Shim pins pack	259044 5
Head length L ₁	25 mm
Shim	259031 27
Lever	259015 9
Lever screw	259018 6
Functional width L ₄	32 mm
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3