

Garant**Clamping toolholder PCSNL 45°, for indexable inserts CN., left-hand, Shank / insert size: 20/09mm****Order data**

Order number	250025 20/09
GTIN	4045197782731
Item class	21T

Technical description

Lever	259015 9
Insert size	9 mm
Functional width L ₄	25 mm
suitable indexable insert	CN.. 09T3..
Shim	259031 27
Head length L ₁	26 mm
Overall length L	125 mm
Shim punches pack	259047 3
Lever screw	259018 6
ISO code toolholder	PCSNR/L 2020K09
Shim pins pack	259044 5
Shank size	20 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3