

**Garant**
**Clamping toolholder PCSNL 45°, for indexable inserts CN., left-hand, Shank / insert size: 25/09mm**

**Order data**

Order number	250025 25/09
GTIN	4045197782748
Item class	21T

**Technical description**

Shim pins pack	259044 5
Lever screw	259018 6
Functional width L <sub>4</sub>	32 mm
ISO code toolholder	PCSNR/L 2525M09
Shank size	25 mm
Insert size	9 mm
Lever	259015 9
Overall length L	150 mm
Head length L <sub>1</sub>	25 mm
Shim punches pack	259047 3
Shim	259031 27
suitable indexable insert	CN.. 09T3..
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3