

**Garant**
**Clamping toolholder SCACR 90°, for indexable inserts CC., right-hand,  
Shank / insert size: 12/06mm**

**Order data**

Order number	260014 12/06
GTIN	4045197797544
Item class	21T

**Technical description**

Pack of insert screws	269021 1
ISO code toolholder	SCACR/L 1212M06
Functional width L <sub>4</sub>	12 mm
suitable indexable insert	CC.. 0602..
Head length L <sub>1</sub>	12 mm
Shank size	12 mm
Overall length L	150 mm
Insert size	6 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7