

Garant

Clamping toolholder SCACL 90°, for indexable inserts CC., left-hand, Shank / insert size: 8/06mm



Order data

Order number	260015 8/06
GTIN	4045197797582
Item class	21T

Technical description

Functional width L_4	8 mm
Head length L_1	8 mm
Overall length L	150 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	SCACR/L 0808M06
Shank size	8 mm
Insert size	6 mm
Pack of insert screws	269021 1
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7