

Garant

Clamping toolholder SDNCN 62,5°, for indexable inserts DC., neutral, Shank / insert size: 12/11mm



Order data

Order number	260301 12/11
GTIN	4045197797971
Item class	21T

Technical description

Overhang L ₁ neutral holders	21 mm
Overall length L neutral holders	150 mm
Pack of insert screws	269021 2
ISO code toolholder	SDNCN 1212M11
Shank size	12 mm
Functional width L ₄ neutral holders	6.2 mm
Insert size	11 mm
suitable indexable insert	DC.. 11T3..
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	62.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 2	269021 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15