

Garant**Clamping toolholder STJCR 93°, for indexable inserts TC., right-hand, Shank / insert size: 12/11mm****Order data**

Order number	260904 12/11
GTIN	4045197798015
Item class	21T

Technical description

Pack of insert screws	269021 1
Overall length L	150 mm
suitable indexable insert	TC.. 1102..
Insert size	11 mm
Functional width L ₄	12 mm
Head length L ₁	16 mm
Shank size	12 mm
ISO code toolholder	STJCR/L 1212M11
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7