

**Garant**
**Clamping toolholder SVACR 90°, for indexable inserts VC., right-hand,  
Shank / insert size: 12/11mm**

**Order data**

Order number	261314 12/11
GTIN	4045197798084
Item class	21T

**Technical description**

suitable indexable insert	VC.. 1103..
Shank size	12 mm
Pack of insert screws	269021 1
Functional width L <sub>4</sub>	12 mm
ISO code toolholder	SVACR/L 1212M11
Insert size	11 mm
Overall length L	150 mm
Head length L <sub>1</sub>	26 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7