

Garant
**Clamping toolholder CRSNR 90°, for indexable inserts RN., right-hand,
Shank / insert size: 32/12mm**

Order data

| | |
|--------------|---------------|
| Order number | 255795 32/12 |
| GTIN | 4045197799111 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-------------------------------|
| Head length L ₁ | 34 mm |
| suitable indexable insert | RN.. 1207.. |
| Clamp | 259035 3 |
| Shank size | 32 mm |
| Functional width L ₄ | 32 mm |
| Insert size | 12 mm |
| ISO code toolholder | CRSNR/L 3225P12 |
| Shim | 259031 43 |
| Shim screw | 259025 2 |
| Overall length L | 170 mm |
| Washer for clamp | 259041 1 |
| Standard | DIN ISO 5610 |
| Application type | right-hand |
| Through-coolant | no |
| Setting angle κ | 90 degrees |
| Application | External longitudinal turning |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Shim screw Type 2 | 259025 2 |
| Shim Type 43 | 259031 43 |
| Clamp unit Type 3 | 259035 3 |
| Washer for clamp Type 1 | 259041 1 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20 | 674248 TX20 |