

Garant
Clamping toolholder CRSNL 90°, for indexable inserts RN., left-hand, Shank / insert size: 32/12mm

Order data

Order number	255796 32/12
GTIN	4045197799135
Item class	21T

Technical description

Head length L ₁	34 mm
Clamp	259035 3
Shim screw	259025 2
Insert size	12 mm
Shank size	32 mm
Overall length L	170 mm
Shim	259031 43
ISO code toolholder	CRSNR/L 3225P12
Functional width L ₄	32 mm
suitable indexable insert	RN.. 1207..
Washer for clamp	259041 1
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim screw Type 2	259025 2
Shim Type 43	259031 43
Clamp unit Type 3	259035 3
Washer for clamp Type 1	259041 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20