

**Burr Z steel – coarse, Carbide, Type: C0616****Order data**

Order number	540740 C0616
GTIN	4045197804785
Item class	52D

Description**Version:**

The innovative tooth geometry permits very high metal removal rates combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank \varnothing 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Technical description

Overall length	50 mm
Shape	C0616
Tooth type abbreviation	Z steel
Shape description	ball nose
Toothing grit designation	coarse
Head \varnothing	6 mm

Shank Ø	6 mm
Head length	18 mm
Series	Tooth configuration Z steel
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		