

**Burr Z steel – coarse, Carbide, Type: C1020****Order data**

Order number	540740 C1020
GTIN	4045197804808
Item class	52D

Description**Version:**

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank Ø 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Technical description

Head Ø	9.6 mm
Toothing grit designation	coarse
Shape	C1020
Shank Ø	6 mm
Overall length	64 mm
Tooth type abbreviation	Z steel

Shape description	ball nose
Head length	19 mm
Series	Tooth configuration Z steel
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		