

HOLEX**Burr Z steel – coarse, Carbide, Type: F0820****Order data**

Order number	540740 F0820
GTIN	4045197804877
Item class	52D

Description**Version:**

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank \varnothing 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Technical description

Shape description	round arch
Tothing grit designation	coarse
Head \varnothing	8 mm
Shape	F0820
Shank \varnothing	6 mm
Overall length	65 mm

Tooth type abbreviation	Z steel
Head length	20 mm
Series	Tooth configuration Z steel
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		