

**Garant****Combination spanner set, Number of keys: 19****Order data**

Order number	613610 19
GTIN	4062406220600
Item class	61A

**Description****Version:**

Drop-forged. With close tolerance jaw width.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance. Ring end with **HT-Drive** profile.

**Standard:**

**DIN 3113 A / ISO 3318 / ISO 7738**

**Material:**

Chrome vanadium steel, chrome-plated.

**Supplied with:**

1 each combination spanner No. 613600 / 613500 / 613800 / 613900 / 613950 / 613520 / 613970:

Size 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24

**Note:**

**HT-Drive** – the particularly close-fitting profile.

**Advantage:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

**Technical description**

Type of product	Spanner
-----------------	---------

## Accessories

Combination spanner Width across flats 24 mm	613600 24
Combination spanner Width across flats 9 mm	613600 9
Combination spanner Width across flats 22 mm	613600 22
Combination spanner Width across flats 6 mm	613600 6
Combination spanner Width across flats 14 mm	613600 14
Combination spanner Width across flats 8 mm	613600 8
Combination spanner Width across flats 5,5 mm	613600 5,5
Combination spanner Width across flats 19 mm	613600 19
Combination spanner Width across flats 13 mm	613600 13
Combination spanner Width across flats 21 mm	613600 21
Combination spanner Width across flats 12 mm	613600 12
Combination spanner Width across flats 16 mm	613600 16
Combination spanner Width across flats 17 mm	613600 17
Combination spanner Width across flats 7 mm	613600 7
Combination spanner Width across flats 18 mm	613600 18
Combination spanner Width across flats 20 mm	613600 20
Combination spanner Width across flats 15 mm	613600 15
Combination spanner Width across flats 11 mm	613600 11
Combination spanner Width across flats 10 mm	613600 10