

Garant**Double open ended spanner set, Number of keys: 12****Order data**

Order number	610610 12
GTIN	4062406220495
Item class	61A

Description**Version:**

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

1 each double open ended spanner No. 610600 / 610100 / 610900 / 610950 / 610120: Size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×23; 24×26; 27×32; 30×34

Technical description

Jaw position 1	15 degrees
Jaw position 2	15 degrees
Type of product	Spanner

Accessories

Double open ended spanner Jaw widths 24X26 mm	610600 24X26
---	--------------

Double open ended spanner Jaw widths 14X15 mm	610600 14X15
Double open ended spanner Jaw widths 16X17 mm	610600 16X17
Double open ended spanner Jaw widths 6X7 mm	610600 6X7
Double open ended spanner Jaw widths 30X34 mm	610600 30X34
Double open ended spanner Jaw widths 21X23 mm	610600 21X23
Double open ended spanner Jaw widths 27X32 mm	610600 27X32
Double open ended spanner Jaw widths 18X19 mm	610600 18X19
Double open ended spanner Jaw widths 20X22 mm	610600 20X22
Double open ended spanner Jaw widths 8X9 mm	610600 8X9
Double open ended spanner Jaw widths 10X11 mm	610600 10X11
Double open ended spanner Jaw widths 12X13 mm	610600 12X13