

Garant

Clamping toolholder STGCL 90°, for indexable inserts TC., left-hand, Shank / insert size: 16/11mm



Order data

Order number	260907 16/11
GTIN	4045197805928
Item class	21T

Technical description

Head length L_1	19 mm
Insert size	11 mm
Overall length L	100 mm
Shank size	16 mm
ISO code toolholder	STGCR/L 1616H11
Functional width L_4	20 mm
Pack of insert screws	269028 18
suitable indexable insert	TC.. 1102..
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 18	269028 18
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15