

Garant
Four-way ratchet ring spanner "4 in 1", Type: 21-27

Order data

| | |
|--------------|---------------|
| Order number | 614847 21-27 |
| GTIN | 4062406229917 |
| Item class | 61B |

Description
Version:

With particularly free-running sturdy ratchet at each end – reversible for left and right hand tightening. The 2 ends have different widths across flats. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Width across flats 1: 21 mm

Width across flats 2: 22 mm

Width across flats 3: 24 mm

Width across flats 4: 27 mm

overall length L: 275 mm

maximum ring \varnothing D1: 40 mm

Technical description

| | |
|-------------------------------|--------|
| maximum ring height h_2 | 30 mm |
| maximum ring \varnothing D1 | 40 mm |
| maximum ring height h_1 | 26 mm |
| Width across flats 4 | 27 mm |
| Width across flats 1 | 21 mm |
| Width across flats | metric |
| Width across flats 3 | 24 mm |
| Width across flats 2 | 22 mm |

| | |
|-------------------------------|-----------------------|
| overall length L | 275 mm |
| maximum ring \varnothing D2 | 52 mm |
| No. of teeth | 72 |
| Working arc | 5° |
| Material | Chrome vanadium steel |
| Surface | matt chrome-plated |
| Ratchet reversible | yes |
| Type of product | Spanner |