

**Garant**
**Four-way ratchet ring spanner "4 in 1", Type: 12-15**

**Order data**

Order number	614847 12-15
GTIN	4062406229900
Item class	61B

**Description**
**Version:**

With particularly free-running sturdy ratchet at each end – reversible for left and right hand tightening. The 2 ends have different widths across flats. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Width across flats 1: 12 mm

Width across flats 2: 13 mm

Width across flats 3: 14 mm

Width across flats 4: 15 mm

overall length L: 190 mm

maximum ring  $\varnothing$  D1: 26.5 mm

**Technical description**

maximum ring $\varnothing$ D1	26.5 mm
Width across flats 1	12 mm
maximum ring height $h_1$	17.1 mm
maximum ring $\varnothing$ D2	29.5 mm
Width across flats	metric
maximum ring height $h_2$	18 mm
Width across flats 4	15 mm
overall length L	190 mm

Width across flats 2	13 mm
Width across flats 3	14 mm
No. of teeth	72
Working arc	5 °
Material	Chrome vanadium steel
Surface	matt chrome-plated
Ratchet reversible	yes
Type of product	Spanner