



Socket set 3/8 inch square drive 19 pieces, Type: 12



Order data

Order number	633918 12
GTIN	4062406230753
Item class	62A

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**. With bi-hexagon sockets.

Application:

For hexagon head screws / nuts with thread M5 – M14.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Sockets: 14 pcs. size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22 mm

T-handle: 1 pc. No. 635720

Extensions: 2 pcs. No. 635420 size 75; 240

Universal joint: 1 pc. No. 636220

Ratchet: 1 pc. No. 635090

Storage in: ABS plastic box

Technical description

Square drive	3/8 in
Width across flats range, bi-hex sockets	8-22 mm
Number of pieces	19
Packaging	ABS plastic box

Length	357 mm
Width	174 mm
Height	47 mm
Type of product	Socket spanner

Accessories

Modular box Type 3	630323 3
Rigid foam inlay for set 633918	630324 633918
Reversible ratchet, 3/8 inch with ejector Type 3/8	635090 3/8
Extension, 3/8 inch overall length 75 mm	635420 75
T-handle, 3/8 inch overall length 200 mm	635720 200
Universal joint, 3/8 inch Type 3/8	636220 3/8