



Pipe welder's clamp, overall length: 280mm



Order data

Order number	709501 280
GTIN	4062406241070
Item class	72B

Description

Version:

U-shaped clamping jaws, the upper jaws have Vee profile to give secure three-point contact when clamping pipes. Sturdy spring steel body. Fully nickel-plated.

Application:

For centralised clamping of pipes and rods when welding.

Material:

Chrome vanadium steel clamping jaws.

Spare part:

Spare spring No. 708301 size 10.

Technical description

Jaw capacity for pipes	2/5 – 2.3/4 in
Jaw capacity for pipes	10 - 70 mm
overall length	280 mm
Jaw capacity a	90 mm
upper gripper jaw	Vee-form
Type of jaws	U-shape - Vee-form
Support	Three-point support
Material of pliers	Spring steel
Material of gripper jaws	Chrome vanadium steel

Surface	nickel-plated
Type of product	Grip wrench

Accessories

Spring Type 10	708301 10
----------------	-----------