

**Hydraulic chuck BASIC short, slim, HSK-A 63, Clamping range $\varnothing$ D1: 8mm****Order data**

Order number	307507 8
GTIN	4062406240097
Item class	32A

Description**Version:**

- Axial length adjustment, adjustment travel 10 mm.
- With RFID/Balluffchip bore.

Application:

- High metal removal rate (but not for extreme heavy machining).
- For drilling, reaming, and milling.

Optional extras:

Reducing sleeves No. 302135 – 302187, coolant tube No. 309880, socket wrench No. 309890, parallel wipers No. 343720.

Note:

A-dimension = 200 mm available on request!

Technical description

Adjustment travel V	10 mm
Overhang dimension A	70 mm
Thread M	M6
L ₃	24 mm
$\varnothing$ D ₂	28 mm
Clamping $\varnothing$ D ₁	8 mm

External Ø D	50 mm
Adapter	HSK-A 63
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Arbor standard	DIN 69882-7
Shape	A
Through-coolant	yes, with max. 80 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Hydraulic clamping chuck

Accessories

Cylindrical cleanerPlastic Pin Ø 8 mm	343720 8
---------------------------------------	----------