



Side lock arbor Form AD, SK 40 A = 160, Clamping range \varnothing D1: 25mm



Order data

| | |
|--------------|---------------|
| Order number | 300277 25 |
| GTIN | 4062406242947 |
| Item class | 32A |

Description

Version:

With Balluff/RFID chip bore.

All shanks fine bead blasted. Balancing quality G 6.3 / 18,000 rpm.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

| | |
|---------------------------------------|----------------------|
| Spare clamping screw No. 30 9900 | 25 |
| Overhang dimension A | 160 mm |
| Clamping \varnothing D ₁ | 25 mm |
| External \varnothing D | 65 mm |
| Adapter | SK 40 A = 160 |
| Standard | DIN 6359 |
| Arbor standard | ISO 7388-1 |
| Shape | AD |
| Balance quality G at rotational speed | G 6.3 at 15,000 rpm |
| Concentricity | $\leq 3 \mu\text{m}$ |

| | |
|--------------------|-----------------|
| Machining strategy | HPC |
| Type of product | Side lock arbor |

Accessories

| | |
|--|-----------|
| Spare clamping screw for chucks with clamping \varnothing D1 25 mm | 309900 25 |
|--|-----------|