



## LED headlamp with rechargeable battery, Type: 300



### Order data

Order number	081493 300
GTIN	4062406242480
Item class	02A

### Description

**Version:**

LED work headlamp with wide spread of light for optimum illumination of the entire work area. Non-contact switching on and off, thanks to sensor system with 2 lighting levels.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

Supplied with USB charging cable.

IP Index of Protection: IP 65

ATEX zone: no

Illumination: 100 lm

Illumination step 2: 300 lm

Working life: 6 h

Lighting life stage 2: 2 h

Number of rechargeable batteries contained: 1

### Technical description

Type of rechargeable battery	Lithium-ion
Overall width	47 mm
Overall length	78 mm
Power supply	Rechargeable battery-powered

Illumination step 2	300 lm
Working life	6 h
IP Index of Protection	IP 65
Illumination	100 lm
Weight	111 g
ATEX zone	no
Number of rechargeable batteries contained	1
Lighting life stage 2	2 h
Type of product	Headlamp