

**HOLEX****Burr set 8 pieces, tooth profile INOX - coarse, Carbide, Number of burrs: 8****Order data**

Order number	547115 8
GTIN	4062406255060
Item class	52D

**Description****Version:**

**The innovative tooth geometry** permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. Outstanding chip formation and surface results, low heat input into the material (no tempering colouration). Shank  $\varnothing$  6mm.

**Application:**

Optimised for use on **austenitic, rust-resistant and acid-resistant steels**, soft titanium alloys and non-ferrous metals.

**Supplied with:**

1 pc. each No. 547250 size A0616; A1020; A1225; C1225; D1009; G0820; F1225; L1020.

**Technical description**

Toothing grit designation	coarse
Tooth type abbreviation	INOX
Tool material	Carbide
Shank $\varnothing$	6 mm

Number of burrs	8
Type of product	Burr

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		

## Accessories

BurrTooth profile INOX – coarse Type D1009	547250 D1009
BurrTooth profile INOX – coarse Type A0616	547250 A0616
BurrTooth profile INOX – coarse Type G0820	547250 G0820
BurrTooth profile INOX – coarse Type F1225	547250 F1225
BurrTooth profile INOX – coarse Type A1225	547250 A1225
BurrTooth profile INOX – coarse Type L1020	547250 L1020
BurrTooth profile INOX – coarse Type C1225	547250 C1225
BurrTooth profile INOX – coarse Type A1020	547250 A1020