

**Small double open ended spanner, Width across flats: 12mm****Order data**

Order number	612205 12
GTIN	4062406260637
Item class	62A

Description**Version:**

With very slim heads. Unequal jaw angles (15° and 75°), same jaw width each end.

Material:

Chrome vanadium steel, chrome-plated.

Technical description

maximum jaw height h	6 mm
Spanner length L	146 mm
Width across flats	metric
Width across flats 1	12 mm
maximum jaw width b1	27.5 mm
Jaw position 1	15 degrees
Jaw position 2	75 degrees
Material	Chromium vanadium steel
Surface	chromium-plated over nickel
Type of product	Spanner