

Garant**Carbide-tipped hammer drill set, Drill Ø: 5-12mm****Order data**

Order number	789015 5-12
GTIN	4062406262976
Item class	71C

Description**Version:**

The distinctive and aggressive centre point permits active centring and optimum guidance during the drilling operation. Innovative head design with short straight lands for significantly faster drilling coupled with significantly improved stability, even in reinforced concrete. Vibration-optimised helical profile with reinforced core. The core diameter and the helix pitch of the drill are precisely matched to each other and ensure efficient transmission of force from the hammer drill to the carbide tip.

Advantage:

- **Short helical lands and concave rake faces (scooping effect) ensure smooth evacuation of the drilling dust.**
- **Wear marks: for evaluation whether the tool is still suitable for drilling holes suitable for insertion of plugs.**
- **Additional specially shaped core cutting edges: efficient fragmentation of concrete.**

Application:

For drilling concrete, natural stone, and masonry - with very high drilling comfort.

Content:

Hammer drill No. 789010: 1 pc. each
size 5; 6; 8, length 110 mm
size 6; 8; 10; 12 length 160 mm

Storage in: Plastic case

Note:

When using extra long drills (> 500 mm), first drill a pilot hole with a shorter drill of the same diameter (prevents bending and breakage).

Technical description

Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

Accessories

Carbide-tipped hammer drill SDS-plus Ø×overall length 6X110 mm	789010 6X110
Carbide-tipped hammer drill SDS-plus Ø×overall length 5X110 mm	789010 5X110
Carbide-tipped hammer drill SDS-plus Ø×overall length 12X160 mm	789010 12X160
Carbide-tipped hammer drill SDS-plus Ø×overall length 8X160 mm	789010 8X160
Carbide-tipped hammer drill SDS-plus Ø×overall length 10X160 mm	789010 10X160
Carbide-tipped hammer drill SDS-plus Ø×overall length 8X110 mm	789010 8X110
Carbide-tipped hammer drill SDS-plus Ø×overall length 6X160 mm	789010 6X160