

Garant

Carbide boring bar E.. SVLCR 95°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 16/07mm


Order data

| | |
|--------------|---------------|
| Order number | 261332 16/07 |
| GTIN | 4062406283575 |
| Item class | 21T |

Technical description

| | |
|--------------------------------------|----------------|
| Insert size | 7 mm |
| Neck width L ₄ | 14.5 mm |
| suitable indexable insert | VC.. 0702.. |
| Clamping height L ₂ | 15 mm |
| Centre offset L ₃ | 11 mm |
| ISO code toolholder | E16M SVLCR/L07 |
| Minimum pre-drill Ø D _{min} | 19.5 mm |
| Overall length L | 150 mm |
| Pack of insert screws | 269028 26 |
| Head length L ₁ | 55 mm |
| Setting angle κ | 95 degrees |
| Usable depth T | 5 mm |
| Shank Ø D _s | 16 mm |
| Standard | Works standard |
| Application type | right-hand |
| Boring depth up to | 8×D |

| | |
|-----------------|-------------------------------|
| Tool material | Carbide |
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring Bar |

Accessories

| | |
|------------------------------|-----------|
| Set of insert screws Type 27 | 269028 27 |
|------------------------------|-----------|