

Garant

Carbide boring bar E.. SVLCL 95°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 8/05mm


Order data

Order number	261333 8/05
GTIN	4062406283582
Item class	21T

Technical description

Insert size	5 mm
Head length L_1	26 mm
Neck width L_4	6 mm
Overall length L	80 mm
ISO code toolholder	E08F SVLCL/L05
Pack of insert screws	269028 27
Setting angle κ	95 degrees
Clamping height L_2	7.5 mm
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Centre offset L_3	5 mm
suitable indexable insert	VC.. 0501..
Usable depth T	3 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------