

Garant

Carbide boring bar E.. SVLCR 95°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 12/07mm


Order data

Order number	261332 12/07
GTIN	4062406283568
Item class	21T

Technical description

Overall length L	125 mm
Neck width L ₄	9 mm
Insert size	7 mm
Minimum pre-drill Ø D _{min}	15.5 mm
Head length L ₁	40 mm
Clamping height L ₂	11 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 26
Setting angle κ	95 degrees
Centre offset L ₃	9 mm
ISO code toolholder	E12K SVLCR/L07
Usable depth T	6 mm
Shank Ø D _s	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------