

Garant

**Carbide boring bar E.. SVVCR 72,5°, for indexable inserts VC.., right-hand,
Shank Ø / insert size: 12/07mm**


Order data

Order number	261336 12/07
GTIN	4062406285548
Item class	21T

Technical description

ISO code toolholder	E12K SVVCR/L07
Pack of insert screws	269028 26
Overall length L	125 mm
Neck width L ₄	9 mm
Clamping height L ₂	11 mm
Centre offset L ₃	9 mm
Head length L ₁	40 mm
Setting angle κ	72.5 degrees
Insert size	7 mm
Minimum pre-drill Ø D _{min}	15.5 mm
suitable indexable insert	VC.. 0702..
Usable depth T	6 mm
Shank Ø D _s	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------