

Garant

Steel boring bar A.. SVXCR 113°, for indexable inserts VC., right-hand, Shank Ø / insert size: 10/07mm


Order data

Order number	261356 10/07
GTIN	4062406285692
Item class	21T

Technical description

Overall length L	100 mm
Insert size	7 mm
Neck width L ₄	6.8 mm
Minimum pre-drill Ø D _{min}	12.5 mm
ISO code toolholder	A10H SVXCR/L07
Clamping height L ₂	9 mm
Head length L ₁	22 mm
Pack of insert screws	269028 26
Centre offset L ₃	7 mm
Setting angle κ	113 degrees
suitable indexable insert	VC.. 0702..
Usable depth T	3 mm
Shank Ø D _s	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------