

Garant

Steel boring bar A.. SVXCR 113°, for indexable inserts VC., right-hand, Shank Ø / insert size: 12/07mm


Order data

Order number	261356 12/07
GTIN	4062406285708
Item class	21T

Technical description

Overhang L_1	36 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Centre offset L_3	9 mm
Insert size	7 mm
suitable indexable insert	VC.. 0702..
ISO code toolholder	A12K SVXCR/L07
Pack of insert screws	269028 26
Clamping height L_2	11 mm
Setting angle κ	113 degrees
Overall length L	125 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------