

**Garant**

**Steel boring bar A.. SVXCR 113°, for indexable inserts VC., right-hand, Shank Ø / insert size: 16/07mm**


**Order data**

Order number	261356 16/07
GTIN	4062406285715
Item class	21T

**Technical description**

Overhang $L_1$	48 mm
Centre offset $L_3$	11 mm
Clamping height $L_2$	15 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
ISO code toolholder	A16M SVXCR/L07
Overall length L	150 mm
Insert size	7 mm
Setting angle $\kappa$	113 degrees
Pack of insert screws	269028 26
suitable indexable insert	VC.. 0702..
Usable depth T	3 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------