

**Garant**

**Steel boring bar A.. SVXCR 113°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 8/05mm**


**Order data**

Order number	261356 8/05
GTIN	4062406285685
Item class	21T

**Technical description**

Neck width $L_4$	6 mm
Head length $L_1$	15 mm
Clamping height $L_2$	7.5 mm
Overall length $L$	80 mm
Pack of insert screws	269028 27
ISO code toolholder	A08F SVXCR/L05
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Insert size	5 mm
Setting angle $\kappa$	113 degrees
suitable indexable insert	VC.. 0501..
Centre offset $L_3$	5 mm
Usable depth $T$	3 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------