

**Garant**

**Steel boring bar A.. SVXCL 113°, for indexable inserts VC.., left-hand, Shank  
Ø / insert size: 12/07mm**


**Order data**

Order number	261357 12/07
GTIN	4062406285746
Item class	21T

**Technical description**

Overall length L	125 mm
Pack of insert screws	269028 26
ISO code toolholder	A12K SVXCR/L07
Clamping height L <sub>2</sub>	11 mm
Minimum pre-drill Ø D <sub>min</sub>	15.5 mm
Overhang L <sub>1</sub>	36 mm
Insert size	7 mm
suitable indexable insert	VC.. 0702..
Setting angle κ	113 degrees
Centre offset L <sub>3</sub>	9 mm
Usable depth T	3 mm
Shank Ø D <sub>s</sub>	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------