

Garant

Steel boring bar A.. SVXCL 113°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 16/07mm


Order data

Order number	261357 16/07
GTIN	4062406285753
Item class	21T

Technical description

Overall length L	150 mm
suitable indexable insert	VC.. 0702..
ISO code toolholder	A16M SVXCR/L07
Overhang L ₁	48 mm
Centre offset L ₃	11 mm
Minimum pre-drill Ø D _{min}	19.5 mm
Insert size	7 mm
Setting angle κ	113 degrees
Pack of insert screws	269028 26
Clamping height L ₂	15 mm
Usable depth T	3 mm
Shank Ø D _s	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------