

Garant

Carbide boring bar E.. SVXCL 113°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 10/07mm



Order data

Order number	261369 10/07
GTIN	4062406285814
Item class	21T

Technical description

Insert size	7 mm
Setting angle κ	113 degrees
ISO code toolholder	E10H SVXCR/L07
suitable indexable insert	VC.. 0702..
Head length L_1	32 mm
Centre offset L_3	7 mm
Neck width L_4	6.8 mm
Clamping height L_2	9 mm
Overall length L	100 mm
Pack of insert screws	269028 26
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------