

**Garant**

**Carbide boring bar E.. SVVCL 72,5°, for indexable inserts VC.., left-hand,  
Shank Ø / insert size: 8/05mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 261337 8/05   |
| GTIN         | 4062406285845 |
| Item class   | 21T           |

**Technical description**

|                               |                |
|-------------------------------|----------------|
| ISO code toolholder           | E08F SVVCR/L05 |
| Clamping height $L_2$         | 7.5 mm         |
| Minimum pre-drill Ø $D_{min}$ | 10.2 mm        |
| suitable indexable insert     | VC.. 0501..    |
| Neck width $L_4$              | 6 mm           |
| Overall length $L$            | 80 mm          |
| Pack of insert screws         | 269028 27      |
| Setting angle $\kappa$        | 72.5 degrees   |
| Centre offset $L_3$           | 5.5 mm         |
| Head length $L_1$             | 26 mm          |
| Insert size                   | 5 mm           |
| Usable depth $T$              | 3,5 mm         |
| Shank Ø $D_s$                 | 8 mm           |
| Standard                      | Works standard |
| Application type              | left-hand      |
| Boring depth up to            | 8xD            |

|                 |                               |
|-----------------|-------------------------------|
| Tool material   | Carbide                       |
| Through-coolant | yes                           |
| Application     | Internal longitudinal turning |
| Type of product | Boring Bar                    |

---

## Accessories

|                              |           |
|------------------------------|-----------|
| Set of insert screws Type 26 | 269028 26 |
|------------------------------|-----------|