

Garant**Fleece velour-backed abrasive disc, Ø 115 mm, Grit equivalent: 280****Order data**

Order number	566911 280
GTIN	4062406297763
Item class	51M

Description**Version:**

Fleece velour-backed abrasive discs with through-stitched backing for hook and loop fastener. With removable centre for more precise positioning and attachment of the disc to the backing pad (**approx. 50 % reduction in vibration level with velour-backed abrasive discs No. 566965**).

Application:

On angle grinders with hook and loop fastener backing pad No. 566960 or 566965. For **finishing, matting, smoothing** with significant reduction in roughness, and for **light cleaning** (such as removal of discolouration) and **deburring tasks**.

Note:

See No. **567705ff** onwards for velour-backed abrasive discs for rough abrasion.

maximum circumferential speed: 40 m/s

Grit designation: fine

Version: A very fine

Colour: blue

Technical description

Grit equivalent	280
-----------------	-----

Version	A very fine
Colour	blue
Grit designation	fine
Disc Ø	115 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
maximum circumferential speed	40 m/s
Type of product	Non-woven abrasive

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		

Accessories

Hook and loop backing pad with Thread M 14 External Ø
115 mm

566960 115

Hook and loop backing pad with Centring and M 14 thread
External Ø 115 mm

566965 115