

**Flap wheel roller, fleece (coarse), Ø 100 × 100 mm, Grit equivalent: CRS****Order data**

Order number	568476 CRS
GTIN	4062406297978
Item class	52M

Description**Version:**

Standard dimensions **Ø 100×100 mm**. Mounting bore Ø 19 mm with multiple splines.

Coarse cleaning fleece, aggressive, with a long working life.

Application:

Quick removal of scale, rust, colouration and paint residues. Uniform surface finish. **Long working life.**

Technical description

Grinding media backing	Rough cleaning non-woven abrasive mesh
recommended speed	2800 min ⁻¹
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Roller Ø	100 mm
Roller width	100 mm
Product name attribute	Ø 100 × 100 mm

Type of product

Fleece coarse cleaning roller

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		