



Lever lock toolholder set, right-hand, Shank size: 20mm



Order data

Order number	255120 20
GTIN	4062406383091
Item class	29W

Technical description

Shank size	20 mm
suitable indexable insert	CN.. 1204..; DN.. 1104..
Functional width L ₄	25 mm
Head length L ₁	28 mm
Spare part	259981 8
ISO code toolholder	PCLNR 2020K12; PDJNR 2020K11;
Overall length L	125 mm
Standard	DIN ISO 5610
Standard	Works standard
Application type	right-hand
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

Accessories

Spare parts set for lever lock toolholder Type 8

259981 8