

Garant**"4 in 1" drilling and turning tool 1.5×D, left-hand, Ø DC: 25mm**

Order data

Order number	268405 25
GTIN	4062406392611
Item class	21K

Description

Version:

Plain shank.

Application:

1. Facing of end faces.
2. Drilling (drilling out and drilling from solid) – flat drilled hole end.
3. Internal longitudinal turning.
4. External longitudinal turning.

Note:

- Choose corner radii and toolholder size as large as possible.
- Drilling tolerance + 0.15 mm (for drilling processes with a driven tool).
- When drilling greater than nominal Ø, residual material will remain.
- Always use internal cooling for drilling (at least 5 bar).

Technical description

Reach L_1	37.5 mm
Nominal Ø D	25 mm
Shank Ø D_s	32 mm
Pack of insert screws	269028 45 (IP20; 5 Nm)
suitable indexable insert	ZCMX 13..
Overall length L	180 mm
Series	"4 in 1"
Application type	left-hand

Through-coolant	yes
Type of product	Boring bar

Accessories

Set of insert screws Type 43	269028 43
Set of insert screws Type 45	269028 45