

Garant

Clamping toolholder SSSCR 45°, for indexable inserts SC., right-hand, Shank / insert size: 16/12mm



Order data

Order number	260706 16/12
GTIN	4062406396817
Item class	21T

Technical description

Head length L_1	18 mm
suitable indexable insert	SC.. 1204..
Shim	269005 9
Functional width L_4	20 mm
Shank size	16 mm
Shim screw	269013 5
Pack of insert screws	269028 20
Insert size	12 mm
ISO code toolholder	SSSCR/L 1616H12
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 9	269005 9
Shim screw Type 5	269013 5
Set of insert screws Type 20	269028 20