

**Garant**
**Clamping toolholder SVHCR 107,5°, for indexable inserts VC., right-hand,  
Shank / insert size: 25/11 mm**

**Order data**

Order number	261308 25/11
GTIN	4062406396831
Item class	21T

**Technical description**

Insert size	11 mm
Overall length L	150 mm
Shank size	25 mm
Head length L <sub>1</sub>	22.9 mm
Pack of insert screws	269028 22
suitable indexable insert	VC.. 1103..
Functional width L <sub>4</sub>	32 mm
ISO code toolholder	SVHCR/L 2525M11
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22

269028 22