

**Garant**
**Clamping toolholder SVHCL 107,5°, for indexable inserts VC., left-hand,  
Shank / insert size: 25/11 mm**

**Order data**

Order number	261309 25/11
GTIN	4062406396848
Item class	21T

**Technical description**

ISO code toolholder	SVHCR/L 2525M11
Head length $L_1$	22.9 mm
Overall length L	150 mm
suitable indexable insert	VC.. 1103..
Shank size	25 mm
Pack of insert screws	269028 22
Functional width $L_4$	32 mm
Insert size	11 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22

269028 22