

Garant

**Carbide boring bar E.. SVJBR 142°, for indexable inserts VB., right-hand,
Shank Ø / insert size: 16/11mm**


Order data

Order number	261112 16/11
GTIN	4062406398019
Item class	21T

Technical description

Head length L_1	31.4 mm
Clamping height L_2	15 mm
Overall length L	200 mm
Setting angle κ	142 degrees
Centre offset L_3	2 mm
Pack of insert screws	269028 7
ISO code toolholder	E16R SVJBR/L 11
Neck width L_4	9.5 mm
suitable indexable insert	VB.. 1103..
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	22 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
-----------------------------	----------