

**Garant**

**Carbide boring bar E.. SVJBR 142°, for indexable inserts VB., right-hand,  
Shank Ø / insert size: 20/11mm**


**Order data**

Order number	261112 20/11
GTIN	4062406398026
Item class	21T

**Technical description**

Setting angle $\kappa$	142 degrees
Pack of insert screws	269028 7
Overall length L	250 mm
Minimum pre-drill $\varnothing D_{\min}$	24 mm
ISO code toolholder	E20S SVJBR/L 11
Head length $L_1$	38 mm
Clamping height $L_2$	19 mm
Neck width $L_4$	11 mm
Centre offset $L_3$	2 mm
Insert size	11 mm
suitable indexable insert	VB.. 1103..
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
-----------------------------	----------